

SMR2.0 10GigE: Recording Camera

SMR2.0SxXGE		
Resolution	1,920 (H) × 1,080 (V) 2 MP	
Diagonal	22.03 mm	
Chroma	Color / Mono	
Pixel size	10µm	
Interface	10GigE	
Frame rate	1.920 x 1.080	2.517 fps
	1.024 x 768	3.531 fps
	512 x 512	5.275 fps
Memory	32 GB	
Dimensions	95 × 95 × 98 mm	
Weight	1.188 g	
Mount	C-Mount, FG-Mount	
Software	VisualMARC3	
IrigB Time Stamp	Optional	
Internal Battery	No	
HiG shock proof	No	



Markets:

Automotive, Electronics & Semiconductor
Medical, Sports, Defense, Food&Beverage
Education (Universitys, Museums)

Applications

- Process optimization
- Trouble shooting
- Quality inspecon

- // Fast download with 10GigE Interface
- // 4,35 seconds recording time in full resolution due to 32GB internal memory
- // Easy to use product specific recording Software VisualMARC3