



Terminal	Wire Harness		Terminal	
Shield	Drain	地線	Shield	
8	Blue	藍	4	Twist
7	Blue/White	白	5	
6	Brown	棕	8	Twist
5	Brown/White	白	7	
4	Green	綠	6	Twist
3	Green/White	白	3	
2	Orange	橙	2	Twist
1	Orange/White	白	1	
P1	Wire Color		P2	
Pin Out				

Twist
Twist
Twist
Twist

Specifications:

1. Poles: 8.
2. Rated Voltage: 48V.
3. Rated Current: 0.5A.
4. Contact resistance: <15mΩ.
5. Insulation resistance: >100MΩ.
6. protection: IP68.
7. Temperature range: -40°C~85°C.
8. Transmission performance(Category): Cat 6A.

RoHS COMPLIANT

1. Housing: Zinc Alloy, Nickel Plated.
2. Nut: Brass, Nickel Plated.
3. Contact: Brass, Gold Over Nickel Plated.
4. Plastic Housing : PBT, Color: Green.
5. Cable: S/FTP 26AWG*4P, LSZH Jacket. OD=φ5.8±0.3mm.

Product code	Length
22506	5000+5%
22507	15000+5%
22508	30000+5%

Importer into the EU

Allied Vision Technologies GmbH
Taschenweg 2a
07646 Stadtroda, Germany

Tel// +49 36428 677-0
Fax// +49 36428 677-28

Manufacturer

Kinsun Industries Inc.
No. 32, Guanye E. Rd., Pingzhen Dist.
Taoyuan City 32457, Taiwan

Tel// +886-3-458-9558



For more information, including instructions to connect this cable, see the
Alecs User Guide at www.alliedvision.com/en/support/alecs-documentation.

設計 DR. Dennis 2022/02/25	核准 APPD. Marco 2022/02/25	容許公差 .XXX ±0.10 .XX ±0.25 .X ±0.38 X ±0.50 ANG ±3°	TOLERANCE	品名 ARTICLE 4007線端一公-8P帶端子
版本說明 REVISION NOTE ---依E302-2202035申請---		圖號 DWG NO. 4007B800D8-0500		單位 UNIT mm
比例 SCALE 1/1		張數 SHEET 1/1	版本 REV. A	

