

APPLICATION NOTE

Bonito PRO Lens Mount Comparison

V1.1.0
2025-Jul-22

Revision history

Version	Date	Remarks
V1.1.0	2025-Jul-22	Updated Chapter Contact us on page 4 and added Chapter Liability, trademarks, and copyright on page 4.
V1.0.0	2018-May-31	Initial release


Table 1: Document history

Introduction


This document compares mount envelope dimensions of Bonito PRO lens mounts. All dimensions are stated in millimeters (mm).

F-Mount

Standard F-Mount (default lens mount) // 02-28XXA // 46.5 mm flange focal distance




Planarity Adjustable F-Mount // 02-28XXA-03 // 46.5 mm flange focal distance




EF-Mount

Planarity Adjustable EF-Mount // 02-28XXA-18 // 44 mm flange focal distance




M42-Mount

Planarity Adjustable M42-Mount // 02-28XXA-25 // 45.46 mm flange focal distance




Standard M42-Mount // 02-28XXA-31 // 45.46 mm flange focal distance




M58-Mount

Planarity Adjustable M58-Mount // 02-28XXA-13 // 46.5 mm flange focal distance



Standard M58-Mount // 02-28XXA-12 // 12.71 mm flange focal distance



Contact us

Website, email

General

www.alliedvision.com/en/contact

info@alliedvision.com

Distribution partners

www.alliedvision.com/en/avt-locations/avt-distributors

Support

www.alliedvision.com/en/support

www.alliedvision.com/en/about-us/contact-us/technical-support-repair/-rma

Offices

Europe, Middle East, and Africa (Headquarters)

Allied Vision Technologies GmbH

Taschenweg 2a

07646 Stadtroda, Germany

T// +49 36428 677-0 (Reception)

T// +49 36428 677-230 (Sales)

F// +49 36428 677-28

North, Central, and South America, Canada

Allied Vision Technologies Canada Inc.

300 – 4621 Canada Way

Burnaby, BC V5G 4X8, Canada

T// +1 604 875 8855

USA

Allied Vision Technologies, Inc.

102 Pickering Way- Suite 502

Exton, PA 19341, USA

Toll-free// +1-877-USA-1394

T// +1 978 225 2030

Asia-Pacific

China

Allied Vision Technologies Shanghai Co Ltd.

B-510, Venture International Business Park

2679 Hechuan Road

Minhang District, Shanghai 201103

People's Republic of China

T// +86 21 64861133

Japan

Allied Vision Technologies

Yokohama Portside Bldg. 10F

8-1 Sakae-cho, Kanagawa-ku

Yokohama-shi, Kanagawa, 221-0052

T// +81 (0) 45 577 9527

Singapore

Allied Vision Technologies Asia Pte. Ltd

82 Playfair Rd, #07-01 D'Lithium

Singapore 368001

T// +65 6634 9027

Liability, trademarks, and copyright

Allied Vision has tested the product under the described conditions. The customer assumes all risk of product damage, application compromise or potential failure, and Sales Warranty loss related to deviation from the described conditions. Allied Vision's acknowledgement of such deviations in the customer's modified product or applications does not constitute advice for use. No Warranty is offered or implied by Allied Vision regarding the customer's assumed risk or legal responsibilities with such modified products or applications.

All text, pictures, and graphics are protected by copyright and other laws protecting intellectual property. All content is subject to change without notice. All trademarks, logos, and brands cited in this document are property and/or copyright material of their respective owners. Use of these trademarks, logos, and brands does not imply endorsement.

Copyright © 2025 Allied Vision Technologies GmbH. All rights reserved.