


Hirose Pinout	
Pin	Signal
1	V OUT- (GND)
2	V OUT+ (24V)
3	IN 4 RxD (RS232)
4	OUT 4 TxD (232)
5	IN 1 (0 - 24V)
6	IN 2 (0 - 24V)
7	OUT 1
8	OUT 2
9	LVDS Input P
10	LVDS Input N
11	LVDS Output P
12	LVDS Output N



NOTICE:
The sensor distance 11,48 mm is compensated for coverglass thickness
Drawing applies to mono and color cameras

		all dimensions in mm unless otherwise specified		Scale: 1:1	Rev.: 1
		Customer Interface Drawing			
Drawn	W. Schreiber	Sign.	Date	Title: EoSens9.5xCX12-M58	
Checked	---	---	---	Material No.: ---	
Material:			Material No.:		
Weight:			A2		
Blatt/Sheet 1 / 1					