bottom view







right view



front view



left view



back view



top view



11,48 optical distance

11,81 optical backfocus
incl. cover glass compensation

12,04 mechanical adjustment
without compensation

	Hirose Pinout ECO, ECO2, EVO, HR
Pin	Signal ECO, ECO2, EVO, HR (CL medium, GigE only)
1	V IN- (GND)
2	V IN+ (10 - 25V)
3	RxD (RS232) not available for Poe version
4	TxD (RS232) not available for Poe version
5	IN 1 (0 - 24V)
6	IN 2 (0 - 24V)
7	OUT 1 (open drain)
8	OUT 2 (open drain)
9	IN 3+ (RS422)
10	IN 3- (RS422)
11	OUT 3+ (RS422)
12	OUT 3+ (RS422)
	Shielding

Hirose Connector



DETAIL - H
MAßSTAB 2 : 1

NOTICE:
- The sensor distance 11,48mm is compansated for coverglass thickness
- drawing applies to mono and color cameras

SVS-VISTEK

all dimensions in mm unless otherwise specified

Scale: 1:1 | Rev.: 1

Customer Interface Drawing

	Name	Sign.	Date
Drawn	W. Schreiber		23.04.2024
Checked			

Title: HR455MXGE-T

Material:

Material No.: F004217-01001

A2

Weight:

Blatt/Sheet 1 / 1