

FXO 25GigE

fxo530M25GE



常规

型号:	fxo530M25GE
产品代码:	F002304
产品系列:	FXO 25GigE
状态:	Available

传感器

传感器类型:	Area scan
色度:	Mono
光谱:	Visible
光谱范围:	400 nm to 1000 nm
分辨率:	5,328 × 4,608 (24.60 MP)
传感器型号:	Sony IMX530AAMJ
传感器架构 (材料) :	cmos
快门类型:	global-shutter
传感器尺寸:	14.60 × 12.63 mm (19.30 mm, 19.3mm (Type 1.2))
像素尺寸:	2.74 µm × 2.74 µm

像素格式

传感器位深度:	8-Bit,12-Bit
单色像素格式:	mono8, mono12

成像性能

动态范围: 72 dB

信噪比: 39 dB

时序与增益

最大帧率: 96 fps

曝光时间: 60 μ s (max)

增益: 0.0 dB to 48.0 dB

I/O与电源

非电气隔离IO: 0 x LVDS input, 0 x LVDS output, 0 x TTL input, 0 x TTL output, 2 x 24V input, 4 x Open drain output,

特定非电气隔离IO: 1 x RS232 input, 1 x RS232 output, 0 x RS422 input, 0 x RS422 output,

光电隔离线路: 1 x Optical isolated input, 0 x Optical isolated input,

电源供应: 10 to 25VDC

功耗: External: 17.5 W (typical)

工作条件

工作温度（外壳: -10 °C to 60 °C

机械特性

机身尺寸（L x W x H mm）: 100 × 50 × 50

滤光片/保护玻璃: K9 - AR coating - 400-850nm

IP防护等级: IP30

镜头接口: C-Mount

重量: 320 g

板载内存与FPGA

图像缓存（RAM）: 4032 MByte

非易失性存储器（闪存）: 128 MByte

接口

数字接口: 25gige

接口连接器: (SFP28)

固件功能 - 图像控制

曝光模式: Manual, Auto, External

固件功能 - 图像控制

增益模式:

Auto, Manual

图像控制功能:

FW Features - Image Control


固件功能 - 相机控制

相机控制功能:

PTP, RDMA support, User Sets, PWM(4), Sequencer,

Monochrome

(not included: lens- and light source characteristics)



I/O pin assignment



1	VIN - (GND)	7	OUT 1 (open drain)
2	VIN + (10 V to 25 V DC)	8	OUT 2 (open drain)
3	IN 4 (RXD RS232)	9	IN 3 + (opto In +)
4	OUT 4 (TXD RS232)	10	IN 3 - (opto In -)
5	IN 1 (0-24V)	11	OUT 3 (open drain)
6	IN 2 (0-24V)	12	OUT 0 (open drain)