



Alvium 1800 U

Alvium 1800 U-131

Alvium 1800 U-131 innovative USB camera with e2v EV76C560 CMOS sensor provides industrial performance for cost effective embedded and machine vision applications.

General

Model	Alvium 1800 U-131
Product series	Alvium 1800 U
Status	Available

Sensor

Sensor type	Area scan
Chroma	Color, Mono
Spectrum	Visible
Spectral range	300 nm to 1100 nm
Resolution	1,280 × 1,024 (1.30 MP)
Sensor model	Teledyne e2v EV76C560
Sensor architecture (material)	cmos
Shutter type(s)	Global shutter (GS)
Sensor size	6.9 × 5.5 mm (8.7 mm, Type 1/1.8)
Pixel size	5.30 µm × 5.30 µm

Pixel formats

Sensor bit depth	10-bit
YUV pixel formats	YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr
RGB pixel formats	BGR8, RGB8 (default)
Bayer pixel formats	BayerRG12

Timing and gain

Max. frame rate	60 fps
Exposure time	16 µs to 1 s

Timing and gain

Gain	0.0 dB to 12.5 dB
------	-------------------

I/Os and power

Non-isolated lines	4 programmable GPIOs
Power supply	Power over USB 3.1 Gen 1 External power 5.0 V
Power consumption	USB power: 1.5 W (typical) Ext. power: 1.5 W (typical)

Operating conditions

Operating temperature (housing)	-20 °C to 65 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	38 × 29 × 29
Lens mount(s)	C-Mount, CS-Mount, S-Mount
Weight	60 g

On-board memory and FPGA

Image buffer (RAM)	256 KByte
Non-volatile memory (Flash)	1024 KByte

Interfaces

Digital interface	usb3.0
Vision standard	USB3 Vision

Quantum Efficiency

 Specifications Image

Technical Drawing

