

Timing and gain

Max. frame rate: 303 fps

I/Os and power

Non-isolated lines: LVTTTL I/Os: 1 input, 1 output

Specific non-isolated lines: 115 200 Baud, 8N1 (adjustable)

Opto-isolated lines: 1 input, 2 outputs

Power supply: 10.8 V to 30.0 V

Power consumption: 21 W at 12 VDC

Operating conditions

Operating temperature (housing): -20 °C to 55 °C (housing)

Mechanical properties

Body dimensions (L x W x H in mm): 90 × 80 × 80

Weight: 740 g


On-board memory and FPGA

Image buffer (RAM): 256 MByte


Interfaces

Digital interface: Camera Link Base

Goldeye G/CL-034 TEC2 Absolute QE



preliminary



preliminary