



# allPIXA pro Camera Link

allPIXA pro 5k

## General

Model	allPIXA pro 5k
Product code	CP000476-5120-W
Product series	allPIXA pro Camera Link
Status	Available

## Sensor

Sensor type	Line scan 2D
Chroma	Color
Spectrum	Visible
Spectral range	400 nm to 1000 nm
Resolution	5,120 × 3 lines
Sensor architecture (material)	ccd
Pixel size	10.00 µm × 10.00 µm

## Pixel formats

Data format	3× 8/10 Bit color
-------------	-------------------

## Timing and gain

Max. line rate tri-linear	40 kHz
---------------------------	--------

## I/Os and power

I/O connector	External IO (15 pin D-Sub, female)
Power supply	12 to 24 VDC
Power consumption	External: 19 W

## Mechanical properties

Body dimensions (L x W x H in mm)	102 × 77 × 100
IP class	IP50
Lens mount(s)	-
Weight	1000 g

## On-board memory and FPGA

Non-volatile memory (Flash)	4 KByte
-----------------------------	---------

## Interfaces

Digital interface	camera link @ 85 mhz full, medium, base
Interface connector	Camera Link (MDR)
Vision standard	Camera Link

## FW features - image control

Exposure modes	manual
Gain modes	auto, manual
White balance modes	auto, manual