



allPIXA pro Camera Link

allPIXA pro 7.3k

General

Model:	allPIXA pro 7.3k
Product code:	CP000476-7300-W
Product series:	allPIXA pro Camera Link
Status:	Available

Sensor

Sensor type:	Line scan 2D
Chroma:	Color
Spectrum:	Visible
Spectral range:	400 nm to 1000 nm
Resolution:	7,300 × 3 lines
Sensor architecture (material):	ccd
Pixel size:	10.00 µm × 10.00 µm

Pixel formats

Data format:	3× 8/10 Bit color
--------------	-------------------

Timing and gain

Max. line rate tri-linear:	29 kHz
----------------------------	--------

I/Os and power

I/O connector:	External IO (15 pin D-Sub, female)
Power supply:	12 to 24 VDC

I/Os and power

Power consumption: External: 19 W

Mechanical properties

Body dimensions (L x W x H in mm): 102 × 77 × 100

IP class: IP50

Lens mount(s): -

Weight: 1000 g

On-board memory and FPGA

Non-volatile memory (Flash): 4 KByte

Interfaces

Digital interface: camera link @ 85 mhz full, medium, base

Interface connector: Camera Link (MDR)

Vision standard: Camera Link

FW features - image control

Exposure modes: manual

Gain modes: auto, manual

White balance modes: auto, manual