


DATA SHEET

Order code:
K1200291

Interface cable


IEEE 1394b 9-pin screw lock
to IEEE 1394b 9-pin screw lock, 15.0 m

V1.0.0
2016-Sep-28



Connector 1


IEEE 1394b 9-pin molded
connector with screw lock




Cable

Connector 2


IEEE 1394b 9-pin molded
connector with screw lock



Cable label



Wiring diagram



Note

Unit in technical drawings is [mm].

Specifications

Feature	Specification
Length	15.0 m ± 100 mm
Diameter	7.2 mm
Classification	Industrial suitability for static applications
Static bending radius	43.2 mm
Dynamic bending radius	For static applications only
Temperature range	On request
Regulations	UL20276, RoHS 2011/65/EU, REACH