


DATA SHEET

Order code:
K1200330

Interface cable



IEEE 1394b 9-pin screw lock
to IEEE 1394b 9-pin screw lock, 2.0 m

V1.0.0
2016-Sep-28




IEEE 1394b 9-pin molded
connector with screw lock


IEEE 1394b 9-pin molded
connector with screw lock



Cable label



Wiring diagram



Note

Unit in technical drawings is [mm].

Specifications

Feature	Specification
Length	2.0 m ± 50 mm
Diameter	7.2 mm
Classification	Industrial suitability for static applications
Static bending radius	43.2 mm
Dynamic bending radius	For static applications only
Temperature range	On request
Regulations	UL20276, RoHS 2011/65/EU, REACH