

Alvium 1800 C

Alvium 1800 C-030 VSWIR



Alvium 1800 C-030 VSWIR innovative MIPI CSI-2 camera with Sony IMX991 SenSWIR InGaAs global shutter sensor provides industrial performance for cost effective embedded vision applications.

General

Model:	Alvium 1800 C-030 VSWIR
Product series:	Alvium 1800 C
Status:	Available

Sensor

Sensor type:	Area scan
Spectrum:	SWIR, Visible SWIR
Spectral range:	400 nm to 1700 nm
Resolution:	656 × 520 (0.30 MP)
Sensor model:	Sony IMX991 InGaAs
Sensor architecture (material):	InGaAs
Shutter type(s):	Global Shutter
Sensor size:	4.61 mm ø (Type 1/4)
Pixel size:	5.00 µm × 5.00 µm

Pixel formats

Monochrome pixel formats:	GREY, Mono8 (default), RAW10, RAW12, RAW8 (default), Y10, Y12
---------------------------	---

Timing and gain

Max. frame rate:	249
------------------	-----

Timing and gain

Exposure time:	15 μ s to 10 s
Gain:	0.0 dB to 42.0 dB

I/Os and power

Non-isolated lines:	2 programmable GPIOs
Power supply:	5 VDC over MIPI CSI-2
Power consumption:	Typical: 1.8 W

Operating conditions

Operating temperature (housing):	-20 °C to 65 °C (housing)
----------------------------------	---------------------------

Mechanical properties

Body dimensions (L x W x H in mm):	26 × 29 × 29
Lens mount(s):	C-Mount, CS-Mount, S-Mount
Weight:	40 g

On-board memory and FPGA

Image buffer (RAM):	256 KByte
Non-volatile memory (Flash):	1024 KByte

Interfaces

Digital interface:	MIPI CSI-2, up to 4 lanes
--------------------	---------------------------

Quantum Efficiency



