Allied Vision

# EXO USB3

## exo265MU3

## General

| | |
|---|---|
| Model | exo265MU3 |
| Product code | F001738 |
| Product series | EXO USB3 |
| Status | Available |

## Sensor

| | |
|---|---|
| Sensor type | Area scan |
| Chroma | Mono |
| Spectrum | Visible |
| Spectral range | 400 nm to 1000 nm |
| Resolution | 2,048 × 1,536 (3.10 MP) |
| Sensor model | Sony IMX265 |
| Sensor architecture (material) | cmos |
| Shutter type(s) | Global shutter (GS) |
| Sensor size | 7.07 × 5.3 mm (8.83 mm, Type 1/1.8) |
| Pixel size | 3.45 µm × 3.45 µm |

## Pixel formats

| | |
|---|---|
| Sensor bit depth | 8-bit, 12-bit |
| Monochrome pixel formats | mono8, mono12packed |

## Imaging performance

| | |
|---|---|
| Dynamic range | 72 dB |
| SNR | 39.95 dB |

## Timing and gain

| | |
|---|---|
| Max. frame rate | 55 fps |
| Exposure time | 24 µs to 60 s |
| Gain | 0.0 dB to 48.0 dB |

## I/Os and power

| | |
|---|---|
| Non-isolated lines | 0 x LVDS input, 0 x LVDS output, 0 x TTL input, 0 x TTL output, 2 x 24V input, 4 x Open drain output, |
| Specific non-isolated lines | 1 x RS232 input, 1 x RS232 output, 0 x RS422 input, 0 x RS422 output, |
| Opto-isolated lines | 1 x Optical isolated input, 0 x Optical isolated input, |
| I/O connector | 12-pin Hirose HR10A-10P-12S |
| Power supply | 10 to 25VDC |
| Power consumption | External: 4.5 W (typical) |

## Operating conditions

| | |
|---|---|
| Operating temperature (housing) | -10 °C to 60 °C |

## Mechanical properties

| | |
|---|---|
| Body dimensions (L x W x H in mm) | 43 × 50 × 50 |
| Filter/protection glass | K9 - AR coating - 400-850nm |
| IP class | IP40 |
| Lens mount(s) | C-Mount |
| Weight | 138 g |

## On-board memory and FPGA

| | |
|---|---|
| Image buffer (RAM) | 192 MByte |
| Non-volatile memory (Flash) | 32 MByte |

## Interfaces

| | |
|---|---|
| Digital interface | usb3.0 |
| Interface connector | (Micro-B) |
| Vision standard | USB3 Vision |

## FW features - image control

| | |
|---|---|
| Exposure modes | manual, auto, external |

## FW features - image control

| | |
|---|---|
| Gain modes | auto, manual |
| Image control features | roi, lut, mirror-image, piv-mode |

## FW features - camera control

| | |
|---|---|
| Trigger modes/sync | internal, software, external |
| Camera control features | User Sets, PWM(4), Sequencer, |

## Quantum Efficiency



Allied Vision

## Technical Drawing

### front




### back




### cross section




### right side



top



bottom






## I/O pin assignment

Hirose 12 Pin



| | | | | | |
|---|---|---|---|---|---|
| 1 | VIN – | (GND) | 7 | OUT 1 | (open drain) |
| 2 | VIN + | (10 V to 25 V DC) | 8 | OUT 2 | (open drain) |
| 3 | IN 4 | (RXD RS232) | 9 | IN 3 + | (opto In +) |
| 4 | OUT 4 | (TXD RS232) | 10 | IN 3 – | (opto In –) |
| 5 | IN 1 | (0 - 24V) | 11 | OUT 3 | (open drain) |
| 6 | IN 2 | (0 - 24V) | 12 | OUT 0 | (open drain) |