Allied Vision

# EXO GigE

## exo428CGE

## General

| | |
|---|---|
| Model | exo428CGE |
| Product code | F002198 |
| Product series | EXO GigE |
| Status | Available |

## Sensor

| | |
|---|---|
| Sensor type | Area scan |
| Chroma | Color |
| Spectrum | Visible |
| Spectral range | 400 nm to 1000 nm |
| Resolution | 3,208 × 2,200 (7.10 MP) |
| Sensor model | Sony IMX428 |
| Sensor architecture (material) | cmos |
| Shutter type(s) | Global shutter (GS) |
| Sensor size | 14.44 × 9.9 mm (17.5 mm, Type 1.1) |
| Pixel size | 4.50 µm × 4.50 µm |

## Pixel formats

| | |
|---|---|
| Sensor bit depth | 8-bit, 12-bit |
| RGB pixel formats | bayer8, bayer12packed |

## Timing and gain

| | |
|---|---|
| Max. frame rate | 17.4 fps |
| Max. frame rate burst | 27 fps |
| Exposure time | 21 µs to 60 s |
| Gain | 0.0 dB to 48.0 dB |

## I/Os and power

| | |
|---|---|
| Non-isolated lines | 0 x LVDS input, 0 x LVDS output, 0 x TTL input, 0 x TTL output, 2 x 24V input, 4 x Open drain output, |
| Specific non-isolated lines | 1 x RS232 input, 1 x RS232 output, 0 x RS422 input, 0 x RS422 output, |
| Opto-isolated lines | 1 x Optical isolated input, 0 x Optical isolated input, |
| I/O connector | 12-pin Hirose HR10A-10P-12S |
| Power supply | 10 to 25VDC, Power over Ethernet |
| Power consumption | External: 5 W (typical) |

## Mechanical properties

| | |
|---|---|
| Body dimensions (L x W x H in mm) | 43 × 50 × 50 |
| Filter/protection glass | IR-Cut - 680nm |
| IP class | IP40 |
| Lens mount(s) | C-Mount |
| Weight | 140 g |

## On-board memory and FPGA

| | |
|---|---|
| Image buffer (RAM) | 192 MByte |
| Non-volatile memory (Flash) | 32 MByte |

## Interfaces

| | |
|---|---|
| Digital interface | gige |
| Interface connector | (RJ-45) |
| Vision standard | GigE Vision |

## FW features - image control

| | |
|---|---|
| Exposure modes | manual, auto, external |
| Gain modes | auto, manual |
| White balance modes | auto, manual |
| Image control features | roi, lut, mirror-image, dpc, shading-correction, ffc |

## FW features - camera control

| | |
|---|---|
| Trigger modes/sync | internal, software, external |
| Camera control features | PTP, BurstMode, User Sets, POE, PWM(4), Sequencer, |

## Quantum Efficiency



Allied Vision

## Technical Drawing

### front




### back




### cross section




### right side



top



bottom




3D



## I/O pin assignment

Hirose 12 Pin



| | | | | | |
|---|---|---|---|---|---|
| 1 | VIN – | (GND) | 7 | OUT 1 | (open drain) |
| 2 | VIN + | (10 V to 25 V DC) | 8 | OUT 2 | (open drain) |
| 3 | IN 4 | (RXD RS232) | 9 | IN 3 + | (opto In +) |
| 4 | OUT 4 | (TXD RS232) | 10 | IN 3 – | (opto In –) |
| 5 | IN 1 | (0 - 24V) | 11 | OUT 3 | (open drain) |
| 6 | IN 2 | (0 - 24V) | 12 | OUT 0 | (open drain) |