

TECHSPEC® COMPACT FIXED FOCAL LENGTH LENS

#58-001 • 12MM FL • F1.8

Designed for use in machine vision applications, our TECHSPEC® Compact Fixed Focal Length Lenses are ideal for use in factory automation, inspection or qualification. These machine vision lenses have been optically designed with the working distance and resolution requirements of factory automation and inspection in mind. Featuring large maximum apertures, these high performance lenses can be used in even the most restrictive lighting conditions. Each lens has a broadband anti-reflection coating, which increases transmission by up to 12 percent over the standard MgF₂ coating on competitive lenses.



Focal Length:	12mm
Minimum Working Distance¹:	200mm
Focus Range¹ (Lockable):	200mm - ∞
Length at Near Focus:	27.9mm
Length at Far Focus:	27.9mm
Filter Thread:	M25.5 x 0.5
Max. Sensor Format:	2/3"
Camera Mount:	C-Mount

Aperture (f/#):	f1.8 - f16
Magnification Range:	0X - 0.055X
Distortion²:	<2.5%
Object Space NA²:	0.007
Number of Elements (Groups):	7 (7)
AR Coating:	425 - 675nm BBAR
Weight:	54g

Sensor Size	1/4"	1/3"	1/2.5"	1/2"	1/1.8"	2/3"	1"	4/3"
Field of View³	64.4mm - 17.2°	85.9mm - 22.9°	102.4mm - 27.0°	115.0mm - 30.3°	130.0mm - 33.5°	159.4mm - 41.1°	N/A	N/A

1. From front of housing 2. At 300mm W.D. 3. Horizontal FOV on standard 4:3 sensor format. Min. W.D. - angular FOV at infinite conjugate

Specifications subject to change




Figure 1: Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




Figure 2: Relative illumination (center to corner)

In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

TECHSPEC® COMPACT FIXED FOCAL LENGTH LENS

#58-001 • 12MM FL • F1.8

MTF & DOF: F2.8
WD: 300MM




Figure 3: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 4: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

TECHSPEC® COMPACT FIXED FOCAL LENGTH LENS

#58-001 • 12MM FL • F1.8

MTF & DOF: F4.0
WD: 300MM




Figure 5: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 6: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

Edmund
optics | worldwide

TECHSPEC® COMPACT FIXED FOCAL LENGTH LENS

#58-001 • 12MM FL • F1.8

MTF & DOF: F2.8
WD: 750MM




Figure 7: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 8: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

Edmund
optics | worldwide

TECHSPEC® COMPACT FIXED FOCAL LENGTH LENS

#58-001 • 12MM FL • F1.8

MTF & DOF: F4.0
WD: 750MM




Figure 9: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are Tangential and Sagittal values for field points on center, at 70% of full field and at the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.






Figure 10: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

Edmund
optics | worldwide



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

*ALSO INCLUDES RECESSED SET SCREW OPTION

FOCAL LENGTH	12.00mm
FOV RANGE ON 2/3" SENSOR	159.4mm - 41.1°
FOV RANGE ON 1/2" SENSOR	115mm - 30.3°
FOV RANGE ON 1/3" SENSOR	85.9mm - 22.9°
WORKING DISTANCE	200mm - ∞
APERTURE (f/#)	F1.8 - F16



Edmund Optics

TITLE	12mm COMPACT FIXED FOCAL LENGTH LENS		
DWG NO	58001	REV	002