

## APPLICATION NOTE

Fixed Pattern Noise Correction  
on Alvium CamerasV1.2.0  
2025-Jul-21

## Scope

This document explains what fixed pattern noise (FPN) is and how the fixed pattern noise correction (FPNC) is calibrated on Alvium cameras.

## FPNC support by model

FPNC support by model is shown in the chapter Image data flow of the corresponding Alvium user guide.

**Alvium user guides**

You can download user guides for the different Alvium cameras at [www.alliedvision.com/en/support/technical-documentation](http://www.alliedvision.com/en/support/technical-documentation).

## What is fixed pattern noise?

Some pixels on a sensor produce brighter intensities than the neighboring pixels. This spatial non-uniformity is called fixed pattern noise. It becomes visible on images acquired in the dark. Inaccuracies in the pixel geometry and the sensor electronics create this effect.

FPN is a high-frequency signal overlaying the image signal. It increases with temperature and exposure time. Though non-uniformities can occur on any individual pixel, issues apply typically to columns, due to readout and amplification. Different sensors have individual characteristics. FPN divides into:

Illumination	Defect	Description
Dark image	Dark signal non-uniformity (DSNU)	Spatial variation of the dark signal
Bright image	Photo response non-uniformity (PRNU)	Spatial variation of the sensitivity

## Example images

The following images show an ideal image (1), column noise and row noise (2), and pixel noise (3):




Figure 1: Ideal image and images with noise

## How are Alvium cameras calibrated for FPNC?

The FPNC on Alvium cameras strives to correct FPN without damaging image details. All Alvium cameras are factory calibrated using the following workflow. Depending on the dominant FPN of the sensor, either row or column noise is being corrected. The following example relates to columns.

For all calibration steps, numerous images are averaged to compensate for temporal noise. In reality all columns of a sensor are corrected, the example shows the photo response of two averaged columns:




Figure 2: Image before correction with two columns. Black level and slope differ.

1. Dark image: DSNU parameters are calculated.




Figure 3: DSNU corrected image. Black level has been aligned, slope differs.

2. Bright image: PRNU parameters are calculated.
3. The corrections align different black levels and slopes.




Figure 4: PRNU corrected image. The columns show equal photo response.

## Contact us

Website, email

### General

[www.alliedvision.com/en/contact](http://www.alliedvision.com/en/contact)

[info@alliedvision.com](mailto:info@alliedvision.com)

### Distribution partners

[www.alliedvision.com/en/avt-locations/avt-distributors](http://www.alliedvision.com/en/avt-locations/avt-distributors)

### Support

[www.alliedvision.com/en/support](http://www.alliedvision.com/en/support)

[www.alliedvision.com/en/about-us/contact-us/technical-support-repair-/rma](http://www.alliedvision.com/en/about-us/contact-us/technical-support-repair-/rma)

## Offices

### Europe, Middle East, and Africa (Headquarters)

Allied Vision Technologies GmbH

Taschenweg 2a

07646 Stadtdroda, Germany

T// +49 36428 677-0 (Reception)

T// +49 36428 677-230 (Sales)

F// +49 36428 677-28

### North, Central, and South America, Canada

Allied Vision Technologies Canada Inc.

300 – 4621 Canada Way

Burnaby, BC V5G 4X8, Canada

T// +1 604 875 8855

### USA

Allied Vision Technologies, Inc.

102 Pickering Way- Suite 502

Exton, PA 19341, USA

Toll-free// +1-877-USA-1394

T// +1 978 225 2030

### Asia-Pacific

#### China

Allied Vision Technologies Shanghai Co Ltd.

B-510, Venture International Business Park

2679 Hechuan Road

Minhang District, Shanghai 201103

People's Republic of China

T// +86 21 64861133

#### Japan

Allied Vision Technologies

Yokohama Portside Bldg. 10F

8-1 Sakae-cho, Kanagawa-ku

Yokohama-shi, Kanagawa, 221-0052

T// +81 (0) 45 577 9527

#### Singapore

Allied Vision Technologies Asia Pte. Ltd

82 Playfair Rd, #07-01 D'Lithium

Singapore 368001

T// +65 6634 9027

## Liability, trademarks, and copyright

Allied Vision has tested the product under the described conditions. The customer assumes all risk of product damage, application compromise or potential failure, and Sales Warranty loss related to deviation from the described conditions. Allied Vision's acknowledgement of such deviations in the customer's modified product or applications does not constitute advice for use. No Warranty is offered or implied by Allied Vision regarding the customer's assumed risk or legal responsibilities with such modified products or applications.

All text, pictures, and graphics are protected by copyright and other laws protecting intellectual property. All content is subject to change without notice. All trademarks, logos, and brands cited in this document are property and/or copyright material of their respective owners. Use of these trademarks, logos, and brands does not imply endorsement.

Copyright © 2025 Allied Vision Technologies GmbH. All rights reserved.