



Mako

Mako G-192

The Mako G-192 is a 1.9 megapixel GigE machine vision camera that incorporates the high quality Type 1/1.8 (9 mm diagonal) Teledyne e2v Sapphire EV76C570 CMOS sensor. At full resolution, this camera runs 60 frames per second. With a smaller region of interest, higher frame rates are possible.

常规

型号:	Mako G-192
产品系列:	Mako
状态:	Available

传感器

传感器类型:	Area scan
色度:	Mono or Color
光谱:	Visible
分辨率:	1,600 × 1,200 (1.90 MP)
传感器型号:	Teledyne e2v EV76C570
传感器架构 (材料) :	CMOS
快门类型:	Global Reset Shutter, Rolling Shutter
传感器尺寸:	9 mm \varnothing (Type 1/1.8)
像素尺寸:	4.50 μm × 4.50 μm

像素格式

传感器位深度:	8-bit or 10-bit
单色像素格式:	Mono8, Mono10
YUV像素格式:	YUV411Packed, YUV422Packed, YUV444Packed
RGB像素格式:	RGB8Packed, BGR8Packed
拜耳像素格式:	BayerGB8, BayerGB10

成像性能

量子效率 @ 529 nm:	43 %
----------------	------

时序与增益

最大帧率: 60 fps

I/O与电源

光电隔离线路: 1 input, 3 outputs

电源供应: 10.8 to 26.4 VDC AUX or 802.3at Type 1 PoE

功耗: 2.1 W at 12 VDC; 2.4 W PoE

工作条件

工作温度 (外壳): 5 °C to 45 °C housing temperature

机械特性

机身尺寸 (L x W x H mm) : 61 × 29 × 29

重量: 80 g

板载内存与FPGA

图像缓存 (RAM) : 64 MByte

非易失性存储器 (闪存) : 1024 KByte

接口

数字接口: IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)

Quantum Efficiency



