



# Goldeye G1

## CL-032 SWIR

- Goldeye CL-032 SWIR NIR camera with InGaAs sensor, 636 × 508 pixels, Peltier cooling

## 基本描述

### NIR camera with InGaAs sensor, 636 x 508 pixels, Peltier cooling

The Goldeye CL-032 NIR is an NIR (near-infrared) camera. It has a spectral response from 900 nm to 1700 nm. Its InGaAs sensor features high sensitivity, very good linearity, and a high damage threshold against intense illumination. The camera is available with Peltier cooling. The Peltier cooling is ideal for applications with long exposure times, or for exact temperature measurements.

Benefits and features:

- InGaAs sensor, spectral range 900 nm to 1700 nm (NIR, near-infrared)
- 14-bit digital processing
- Camera Link interface
- 30 fps/30 Hz
- Peltier cooling for long exposure times and exact temperature measurements
- C-Mount (Goldeye CL-32 NIR Cool)
- F-Mount (Goldeye CL-032 NIR F-Mount Cool)


Models:

Goldeye CL-032 NIR Cool

## 性能参数

Goldeye G1	CL-032 SWIR
接口	Camera Link Base
分辨率	636 (H) × 508 (V)

Goldeye G1	CL-032 SWIR
传感器	InGaAs FPA 636 x 508
传感器类型	InGaAs
像元尺寸	25 $\mu\text{m}$ x 25 $\mu\text{m}$
镜头接口	C-Mount, F-Mount
分辨率下最高帧速	30 fps
ADC	0 bit
缓存 (RAM)	
	输出
Bit位数	bit
	工作条件/尺寸
符合规范	CE (2004/108/EC), RoHS (2011/65/EU), WEEE (2012/19/EU), FCC Class B



## 特性

- Gain, up to factor 20 at short exposure times
- Exposure time 64  $\mu\text{s}$  to 1 s
- Shipped with built-in correction data sets
- Gain/offset correction (NUC / non-uniformity correction) for each pixel
- Bad pixel correction
- Background (FPN) correction
- Continuous mode (image acquisition with maximum frame rate)
- Image On Demand mode (triggered image acquisition)



In combination with Allied Vision's AcquireControl software, extensive image analysis functions are available:

- Pseudo color LUT with several color profiles
- Auto contrast
- Auto brightness
- Analyze multiple regions (rectangular, circle) within the image
- Real-time statistics and histogram display



## 应用场景

Goldeye NIR cameras are very sensitive in the NIR spectrum, show excellent linearity, and tolerate intense illumination. They are the perfect choice for numerous NIR applications:

- Near-infrared imaging
- Thermal imaging of hot objects (in a range of 250°C to 800°C)
- Imaging spectroscopy
- Laser beam profiling
- Sorting according to plastic
- Semiconductor inspection
- Water or moisture detection
- Medical science and biology
- Vision enhancement