

Prosilica GT

Prosilica GT 2050

Prosilica GT2050 is a 4.2 megapixel camera with a GigE Vision compliant Gigabit Ethernet port and Hirose I/O port. Prosilica GT2050 is offered in both monochrome and color models. This camera incorporates the high quality CMOSIS/ams CMV4000 sensor.

Allgemein

Modell	Prosilica GT 2050
Produktserie	Prosilica GT
Status	Available

Sensor

Sensortyp	Area scan
Chroma	Mono or Color
Spektrum	Visible
Auflösung	2,048 × 2,048 (4.20 MP)
Sensormodell	CMOSIS/ams CMV4000
Sensorarchitektur (Material)	CMOS
Verschlusstyp(en)	Global Shutter
Sensorgröße	16.3 mm ø (Type 1)
Pixelgröße	5.50 µm × 5.50 µm

Pixelformate

Sensor-Bittiefe	8-bit or 12-bit
Monochrome Pixelformate	Mono8, Mono12, Mono12Packed
YUV-Pixelformate	YUV411Packed, YUV422Packed, YUV444Packed
RGB-Pixelformate	RGB8Packed, BGR8Packed, RGBA8Packed, BGRA8Packed
Bayer-Pixelformate	BayerGB8, BayerGB12, BayerGB12Packed

Bildgebungsleistung

Quanteneffizienz @ 529 nm	79 %
---------------------------	------

Timing und Verstärkung

Max. Bildrate	28 fps
---------------	--------

I/Os und Stromversorgung

Nicht-isolierte Leitungen	1 input, 2 outputs
Spezifische nicht-isolierte Leitungen	1
Optisch isolierte Leitungen	1 input, 2 outputs
Stromversorgung	7 to 25 VDC AUX or 802.3at Type 1 PoE
Stromverbrauch	3.5 W at 12 VDC; 4.3 W PoE

Betriebsbedingungen

Betriebstemperatur (Gehäuse)	-20 °C to 65 °C (ambient (without condensation))
------------------------------	--

Mechanische Eigenschaften

Gehäuseabmessungen (L x B x H in mm)	86 × 53 × 33
Gewicht	210 g


Onboard-Speicher und FPGA

Bildpuffer (RAM)	128 MByte
Nichtflüchtiger Speicher (Flash)	1024 KByte

Schnittstellen

Digitale Schnittstelle	IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)
------------------------	---

Quanteneffizienz



Technische Zeichnung

