



Alecs G1-1242 innovative vision system with Sony IMX545 CMOS global shutter sensor and NVIDIA® Jetson Orin™ Nano8 enables developing applications faster. The NVIDIA® Jetson Orin™ Nano8 embedded board provides 8 GByte RAM, with power modes up to 25 W. This vision systems extends the Alvium BSP feature set by NVIDIA vision libraries. Alecs G1 comes with 128GByte NVMe storage, providing sufficient space for AI models, datasets, and application software.

Allgemein

Modell	Alecs G1-1242 NA8
Produktserie	Alecs
Status	Available

Sensor

Sensortyp	Area scan
Chroma	Color, Mono
Spektrum	Visible
Spektralbereich	300 nm to 1100 nm
Auflösung	4,128 × 3,008 (12.40 MP)
Sensormodell	Sony IMX545
Sensorarchitektur (Material)	cmos
Verschlusstyp(en)	Global shutter (GS)
Sensorgröße	11.3 × 8.2 mm (14 mm, Type 1/1.1)
Pixelgröße	2.74 µm × 2.74 µm

Pixelformate

Sensor-Bittiefe	12-bit
Monochrome Pixelformate	GREY, RAW10, RAW12, RAW8, Y10, Y12
YUV-Pixelformate	UYVY, YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr, YUV422 8-bit
RGB-Pixelformate	BGR8, RGB3, RGB8 (default), RGB888 (default)

Pixelformate

Bayer-Pixelformate	BayerRG12
--------------------	-----------

Bildgebungsleistung

Quanteneffizienz @ 529 nm	68 %
---------------------------	------

Timing und Verstärkung

Max. Bildrate	40 fps
Belichtungszeit	11 μ s to 10 s
Verstärkung	0.0 dB to 48.0 dB

I/Os und Stromversorgung

Nicht-isolierte Leitungen	2 inputs, 2 outputs, 1 trigger input, 1 strobe output
Stromversorgung	24 VDC
Stromverbrauch	SoM: Max. 10 W to 25 W Carrier board: Max. 2.0 W Camera: Max. 3.2 W Idle state: 8.5 W

Betriebsbedingungen

Betriebstemperatur (Gehäuse)	-20 °C to 65 °C ((housing))
------------------------------	-----------------------------

Mechanische Eigenschaften

Gehäuseabmessungen (L x B x H in mm)	102 × 72 × 112
Objektivanschluss/-anschlüsse	C-Mount
Gewicht	810 g


Onboard-Speicher und FPGA

Bildpuffer (RAM)	256 KByte
Nichtflüchtiger Speicher (Flash)	1024 KByte

Schnittstellen

Digitale Schnittstelle	IEEE 802.3 1000BASE-T
------------------------	-----------------------

Quanteneffizienz



Technische Zeichnung

Alecs Main Housing with Lens Tube LT4649

