



# Alvium C

## Alvium 1800 C-030 VSWIR

Alvium 1800 C-030 VSWIR innovative MIPI CSI-2 camera with Sony IMX991 SenSWIR InGaAs global shutter sensor provides industrial performance for cost effective embedded vision applications.

### General

Model	Alvium 1800 C-030 VSWIR
Product series	Alvium C
Status	Available

### Sensor

Sensor type	Area scan
Spectrum	SWIR, Visible SWIR
Spectral range	400 nm to 1700 nm
Resolution	656 × 520 (0.30 MP)
Sensor model	Sony IMX991   InGaAs
Sensor architecture (material)	InGaAs
Shutter type(s)	Global Shutter
Sensor size	4.61 mm ø (Type 1/4)
Pixel size	5.00 µm × 5.00 µm

### Pixel formats

Monochrome pixel formats	GREY, Mono8 (default), RAW10, RAW12, RAW8 (default), Y10, Y12
--------------------------	---

### Timing and gain

Max. frame rate	249 fps
Exposure time	15 µs to 10 s
Gain	0.0 dB to 42.0 dB

## I/Os and power

Non-isolated lines	2 programmable GPIOs
Power supply	5 VDC over MIPI CSI-2
Power consumption	Typical: 1.8 W

## Operating conditions

Operating temperature (housing)	-20 °C to 65 °C ((housing))
---------------------------------	-----------------------------

## Mechanical properties

Body dimensions (L x W x H in mm)	26 × 29 × 29
Lens mount(s)	C-Mount, CS-Mount, S-Mount
Weight	40 g


## On-board memory and FPGA

Image buffer (RAM)	256 KByte
Non-volatile memory (Flash)	1024 KByte

## Interfaces

Digital interface	MIPI CSI-2, up to 4 lanes
-------------------	---------------------------

## Quantum Efficiency



Technical Drawing

