



Alvium C

Alvium 1800 C-130 VSWIR

Alvium 1800 C-130 VSWIR innovative MIPI CSI-2 camera with Sony IMX990 SenSWIR InGaAs global shutter sensor provides industrial performance for cost effective embedded vision applications.

General

Model	Alvium 1800 C-130 VSWIR
Product series	Alvium C
Status	Available

Sensor

Sensor type	Area scan
Chroma	Mono
Spectrum	SWIR, Visible SWIR
Spectral range	400 nm to 1700 nm
Resolution	1,296 × 1,032 (1.30 MP)
Sensor model	Sony IMX990 InGaAs
Sensor architecture (material)	cmos-ingaas
Shutter type(s)	Global shutter (GS)
Sensor size	6.4 × 5.1 mm (8.2 mm, Type 1/2)
Pixel size	5.00 µm × 5.00 µm

Pixel formats

Sensor bit depth	10-bit, 12-bit, 8-bit
Monochrome pixel formats	GREY, Mono8 (default), RAW10, RAW12, RAW8 (default), Y10, Y12

Timing and gain

Max. frame rate	130 fps
Exposure time	15 µs to 10 s
Gain	0.0 dB to 42.0 dB

I/Os and power

Non-isolated lines	2 programmable GPIOs
Power supply	5 VDC over MIPI CSI-2
Power consumption	Typical: 1.9 W

Operating conditions

Operating temperature (housing)	-20 °C to 55 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	26 × 29 × 29
Lens mount(s)	C-Mount, CS-Mount, S-Mount
Weight	40 g


On-board memory and FPGA

Image buffer (RAM)	256 KByte
Non-volatile memory (Flash)	1024 KByte

Interfaces

Digital interface	MIPI CSI-2, up to 4 lanes
-------------------	---------------------------

Quantum Efficiency



Technical Drawing

