



Alvium C

Alvium 1800 C-320 VSWIR

Alvium 1800 C-320 VSWIR innovative MIPI CSI-2 camera with Sony IMX993 SenSWIR InGaAs global shutter sensor provides industrial performance for cost effective embedded vision applications.

General

Model	Alvium 1800 C-320 VSWIR
Product series	Alvium C
Status	Available

Sensor

Sensor type	Area scan
Spectrum	SWIR, Visible SWIR
Spectral range	400 nm to 1700 nm
Resolution	2,080 × 1,544 (3.20 MP)
Sensor model	Sony IMX993 InGaAs
Sensor architecture (material)	InGaAs
Shutter type(s)	Global Shutter
Sensor size	9 mm ø (Type 1/1.8)
Pixel size	3.45 µm × 3.45 µm

Pixel formats

Monochrome pixel formats	GREY, RAW10, RAW12, RAW8, Y10, Y12
--------------------------	------------------------------------

Timing and gain

Max. frame rate	131 fps
Exposure time	33 µs to 10 s
Gain	0.0 dB to 42.0 dB

I/Os and power

Non-isolated lines	2 programmable GPIOs
Power supply	5 VDC over MIPI CSI-2
Power consumption	Typical: 2.6 W

Operating conditions

Operating temperature (housing)	-20 °C to 65 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	26 × 29 × 29
Lens mount(s)	C-Mount, CS-Mount
Weight	40 g

On-board memory and FPGA

Image buffer (RAM)	256 KByte
Non-volatile memory (Flash)	1024 KByte

Interfaces

Digital interface	MIPI CSI-2, up to 4 lanes
-------------------	---------------------------

Quantum Efficiency



Technical Drawing

