



# Alvium FP3

## Alvium FP3-2460

Alvium FP3-2460 innovative FPD-Link III camera with Sony IMX540 CMOS global shutter sensor provides industrial performance for cost effective embedded applications.

### General

|                |                 |
|----------------|-----------------|
| Model          | Alvium FP3-2460 |
| Product series | Alvium FP3      |
| Status         | Available       |

### Sensor

|                 |                          |
|-----------------|--------------------------|
| Sensor type     | Area scan                |
| Chroma          | Mono or Color            |
| Spectrum        | Visible                  |
| Spectral range  | 300 nm to 1100 nm        |
| Resolution      | 5,328 × 4,608 (24.60 MP) |
| Sensor model    | Sony IMX540              |
| Shutter type(s) | Global Shutter           |
| Sensor size     | 21.43 mm ø (Type 1.2)    |
| Pixel size      | 2.74 µm × 2.74 µm        |

### Pixel formats

|                          |                                                                          |
|--------------------------|--------------------------------------------------------------------------|
| Monochrome pixel formats | GREY, RAW10, RAW12, RAW8, Y10, Y12                                       |
| YUV pixel formats        | UYVY, YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr, YUV422 8-bit |
| RGB pixel formats        | BGR8, RGB3, RGB8 (default), RGB888 (default)                             |
| Bayer pixel formats      | BayerGR10, BayerGR10p, BayerGR12, BayerGR12p, BayerGR8                   |

### Imaging performance

|                             |      |
|-----------------------------|------|
| Quantum efficiency @ 529 nm | 68 % |
|-----------------------------|------|

## Timing and gain

|                 |                                                   |
|-----------------|---------------------------------------------------|
| Max. frame rate | Mainly depends on hardware and register settings. |
| Exposure time   | 13 $\mu$ s to 10 s                                |
| Gain            | 0.0 dB to 48.0 dB                                 |

## I/Os and power

|                    |                                                                |
|--------------------|----------------------------------------------------------------|
| Non-isolated lines | 2 programmable GPIOs                                           |
| I/O connector      | Coax, STP                                                      |
| Power supply       | 5 VDC over MIPI CSI-2                                          |
| Power consumption  | Value for the integrated serializer adds to CSI-2 model value. |

## Operating conditions

|                                 |                             |
|---------------------------------|-----------------------------|
| Operating temperature (housing) | -20 °C to 65 °C ((housing)) |
|---------------------------------|-----------------------------|

## Mechanical properties

|                                   |                   |
|-----------------------------------|-------------------|
| Body dimensions (L x W x H in mm) | 41 × 29 × 29      |
| Lens mount(s)                     | C-Mount, CS-Mount |
| Weight                            | 70 g              |

## On-board memory and FPGA

|                             |            |
|-----------------------------|------------|
| Image buffer (RAM)          | 256 KByte  |
| Non-volatile memory (Flash) | 1024 KByte |

## Interfaces

|                   |                                                  |
|-------------------|--------------------------------------------------|
| Digital interface | FPD-Link III, based on MIPI CSI-2, up to 4 lanes |
|-------------------|--------------------------------------------------|

## Quantum Efficiency



## Technical Drawing

