

# Alvium G1

## Alvium G1-1236



Alvium G1-1236 innovative GigE camera with Sony IMX304 CMOS global shutter sensor provides industrial performance for cost effective embedded and machine vision applications.

### General

Model:	Alvium G1-1236
Product series:	Alvium G1
Status:	Available

### Sensor

Sensor type:	Area scan
Chroma:	Mono or Color
Spectrum:	Visible
Spectral range:	300 nm to 1100 nm
Resolution:	4,112 × 3,008 (12.40 MP)
Sensor model:	Sony IMX304
Sensor architecture (material):	CMOS
Shutter type(s):	Global Shutter
Sensor size:	17.6 mm ø (Type 1.1)
Pixel size:	3.45 µm × 3.45 µm

### Pixel formats

Sensor bit depth:	12-bit
Monochrome pixel formats:	Mono8, Mono10, Mono10p, Mono12, Mono12p, Mono12Packed
YUV pixel formats:	YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr

## Pixel formats

RGB pixel formats:	RGB8 (default), BGR8
Bayer pixel formats:	BayerRG8, BayerRG10, BayerRG10p, BayerRG12, BayerRG12p, BayerRG12Packed

## Imaging performance

Quantum efficiency @ 529 nm:	64 %
------------------------------	------

## Timing and gain

Max. frame rate:	9
------------------	---

## I/Os and power

Non-isolated lines:	2 GPIOs (LVTTL)
Opto-isolated lines:	1 input, 1 output
Power supply:	10.8 to 26.4 VDC AUX   IEEE 802.3af, Power Class 0 PoE
Power consumption:	External power: 3.8 W at 12 VDC (typical)   Power over Ethernet: 4.0 W (typical)

## Operating conditions

Operating temperature (housing):	-20 °C to 65 °C (housing)
----------------------------------	---------------------------

## Mechanical properties

Body dimensions (L x W x H in mm):	41 × 29 × 29
Lens mount(s):	C-Mount, CS-Mount
Weight:	70 g


## On-board memory and FPGA

Image buffer (RAM):	32 MByte
Non-volatile memory (Flash):	1024 KByte

## Interfaces

Digital interface:	IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)
--------------------	---

# Quantum Efficiency



# Technical Drawing

