

Alvium G1

Alvium G1-040



Alvium G1-040 innovative GigE camera with Sony IMX287 CMOS global shutter sensor provides industrial performance for cost effective embedded and machine vision applications.

General

Model:	Alvium G1-040
Product series:	Alvium G1
Status:	Available

Sensor

Sensor type:	Area scan
Chroma:	Mono or Color
Spectrum:	Visible
Spectral range:	300 nm to 1100 nm
Resolution:	728 × 544 (0.40 MP)
Sensor model:	Sony IMX287
Sensor architecture (material):	CMOS
Shutter type(s):	Global Shutter
Sensor size:	6.3 mm ø (Type 1/2.9)
Pixel size:	6.90 µm × 6.90 µm

Pixel formats

Sensor bit depth:	8-bit, 10-bit, 12-bit; Adaptive (10-bit, 12-bit)
Monochrome pixel formats:	Mono8, Mono10, Mono10p, Mono12, Mono12p, Mono12Packed
YUV pixel formats:	YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr

Pixel formats

RGB pixel formats: RGB8 (default), BGR8

Bayer pixel formats: BayerRG8, BayerRG10, BayerRG10p, BayerRG12, BayerRG12p, BayerRG12Packed

Imaging performance

Quantum efficiency @ 529 nm: 64 %

Timing and gain

Max. frame rate: 298 fps

I/Os and power

Non-isolated lines: 2 GPIOs (LVTTL)

Opto-isolated lines: 1 input, 1 output

Power supply: 10.8 to 26.4 VDC AUX | IEEE 802.3af, Power Class 0 PoE

Power consumption: External power: 3.1 W at 12 VDC (typical) | Power over Ethernet: 3.4 W (typical)

Operating conditions

Operating temperature (housing): -20 °C to 65 °C (housing)

Mechanical properties

Body dimensions (L x W x H in mm): 41 × 29 × 29

Lens mount(s): C-Mount, CS-Mount, S-Mount

Weight: 70 g

On-board memory and FPGA


Image buffer (RAM): 32 MByte

Non-volatile memory (Flash): 1024 KByte

Interfaces

Digital interface: IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)

Quantum Efficiency



Technical Drawing

