

Alvium G5

Alvium G5-130 VSWIR



Alvium G5-130 VSWIR innovative 5GBASE-T camera with global shutter Sony IMX990 SenSWIR InGaAs sensor enables short wave infrared (SWIR) imaging with industrial performance for various machine vision applications.

General

Model:	Alvium G5-130 VSWIR
Product series:	Alvium G5
Status:	Available

Sensor

Sensor type:	Area scan
Chroma:	Mono
Spectrum:	SWIR, Visible SWIR
Spectral range:	400 nm to 1700 nm
Resolution:	1,296 × 1,032 (1.30 MP)
Sensor model:	Sony IMX990 InGaAs
Sensor architecture (material):	InGaAs
Shutter type(s):	Global Shutter
Sensor size:	8.15 mm ø (Type 1/2)
Pixel size:	5.00 µm × 5.00 µm

Pixel formats

Sensor bit depth:	8-bit, 10-bit, 12-bit; Adaptive (10-bit, 12-bit)
Monochrome pixel formats:	Mono8 (default), Mono10, Mono10p, Mono12, Mono12p, Mono12Packed

Timing and gain

Max. frame rate: 130 fps

I/Os and power

Non-isolated lines: 2 GPIOs (LVTTTL)

Opto-isolated lines: 1 input, 1 output

Power supply: 10.8 to 26.4 VDC AUX | IEEE 802.3af, Power Class 0 PoE

Power consumption: External power: 4.9 W at 12 VDC (typical) | Power over Ethernet: 5.7 W (typical)

Operating conditions

Operating temperature (housing): -20 °C to 60 °C housing temperature

Mechanical properties

Body dimensions (L x W x H in mm): 60 × 29 × 29

Lens mount(s): C-Mount, CS-Mount, S-Mount

Weight: 100 g

On-board memory and FPGA

Image buffer (RAM): 512 MByte

Non-volatile memory (Flash): 1024 KByte

Interfaces

Digital interface: IEEE 802.3: 5GBASE-T or 2.5GBASE-T (NBASE-T) and 1000BASE-T, IEEE 802.3af Power Class 0 PoE

Quantum Efficiency



