

Alvium G5

Alvium G5-2050



Alvium G5-2050 innovative 5GBASE-T camera with Sony IMX183 CMOS rolling shutter sensor provides industrial performance for cost effective machine vision applications.

General

Model:	Alvium G5-2050
Product series:	Alvium G5
Status:	Available

Sensor

Sensor type:	Area scan
Chroma:	Mono or Color
Spectral range:	300 nm to 1100 nm
Resolution:	5,496 × 3,672 (20.20 MP)
Sensor model:	Sony IMX183
Shutter type(s):	Global Reset Shutter, Rolling Shutter
Sensor size:	16.3 mm ø (Type 1)
Pixel size:	2.40 µm × 2.40 µm

Pixel formats

YUV pixel formats:	YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr
RGB pixel formats:	BGR8, RGB8 (default)
Bayer pixel formats:	BayerRG12

Imaging performance

Quantum efficiency @ 529 nm:	80 %
------------------------------	------

Timing and gain

Max. frame rate: 26 fps

I/Os and power

Non-isolated lines: 2 GPIOs (LVTTTL)

Opto-isolated lines: 1 input, 1 output

Power supply: 10.8 to 26.4 VDC AUX | IEEE 802.3af, Power Class 0 PoE

Power consumption: External power: 6.5 W at 12 VDC (typical) | Power over Ethernet: 7.0 W (typical)

Operating conditions

Operating temperature (housing): -20 °C to 60 °C housing temperature

Mechanical properties

Body dimensions (L x W x H in mm): 60 × 29 × 29

Lens mount(s): C-Mount, CS-Mount

Weight: 100 g

On-board memory and FPGA

Image buffer (RAM): 512 MByte

Non-volatile memory (Flash): 1024 KByte

Interfaces

Digital interface: IEEE 802.3: 5GBASE-T or 2.5GBASE-T (NBASE-T) and 1000BASE-T, IEEE 802.3af Power Class 0 PoE

Quantum Efficiency



