

# Alvium G5

Alvium G5-508



Alvium G5-508 innovative 5GBASE-T camera with Sony IMX250 CMOS global shutter sensor provides industrial performance for cost effective machine vision applications.

## General

Model:	Alvium G5-508
Product series:	Alvium G5
Status:	Available

## Sensor

Sensor type:	Area scan
Chroma:	Mono or Color
Spectrum:	Visible
Spectral range:	300 nm to 1100 nm
Resolution:	2,464 × 2,056 (5.10 MP)
Sensor model:	Sony IMX250
Sensor architecture (material):	CMOS
Shutter type(s):	Global Shutter
Sensor size:	12.75 mm ø (Type 2/3)
Pixel size:	3.45 µm × 3.45 µm

## Pixel formats

Sensor bit depth:	8-bit, 10-bit, 12-bit; Adaptive (10-bit, 12-bit)
Monochrome pixel formats:	Mono8, Mono10, Mono10p, Mono12, Mono12p, Mono12Packed
YUV pixel formats:	YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr
RGB pixel formats:	RGB8 (default), BGR8

## Pixel formats

Bayer pixel formats:

BayerRG8, BayerRG10, BayerRG10p, BayerRG12, BayerRG12p, BayerRG12Packed

## Imaging performance

Quantum efficiency @ 529 nm:

64 %

## Timing and gain

Max. frame rate:

95 fps

## I/Os and power

Non-isolated lines:

2 GPIOs (LVTTTL)

Opto-isolated lines:

1 input, 1 output

Power supply:

10.8 to 26.4 VDC AUX | IEEE 802.3af, Power Class 0 PoE

Power consumption:

External power: 6.1 W at 12 VDC (typical) | Power over Ethernet: 7.0 W (typical)

## Operating conditions

Operating temperature (housing):

-20 °C to 60 °C housing temperature

## Mechanical properties

Body dimensions (L x W x H in mm):

60 × 29 × 29

Lens mount(s):

C-Mount, CS-Mount

Weight:

100 g

## On-board memory and FPGA

Image buffer (RAM):

512 MByte

Non-volatile memory (Flash):

1024 KByte

## Interfaces

Digital interface:

IEEE 802.3: 5GBASE-T or 2.5GBASE-T (NBASE-T) and 1000BASE-T, IEEE 802.3af Power Class 0 PoE

# Quantum Efficiency



