



Alvium GM2

Alvium GM2-319

Alvium GM2-319 innovative GMSL2 camera with Sony IMX265 CMOS global shutter sensor provides industrial performance for cost effective embedded vision applications.

General

Model	Alvium GM2-319
Product series	Alvium GM2
Status	Available

Sensor

Sensor type	Area scan
Chroma	Mono or Color
Spectrum	Visible
Spectral range	300 nm to 1100 nm
Resolution	2,064 × 1,544 (3.20 MP)
Sensor model	Sony IMX265
Sensor architecture (material)	CMOS
Shutter type(s)	Global Shutter
Sensor size	9 mm ø (Type 1/1.8)
Pixel size	3.45 µm × 3.45 µm

Pixel formats

Sensor bit depth	12-bit
Monochrome pixel formats	Mono8, Mono10, Mono10p, Mono12, Mono12p, RAW8, RAW10, RAW12, GREY, Y10, Y12
YUV pixel formats	YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr, YUV422 8-bit, UYVY
RGB pixel formats	RGB8 (default), BGR8, RGB888 (default), RGB3
Bayer pixel formats	BayerGR8, BayerGR10, BayerGR10p, BayerGR12, BayerGR12p

Imaging performance

Quantum efficiency @ 529 nm	64 %
-----------------------------	------

Timing and gain

Max. frame rate	Mainly depends on hardware and register settings.
-----------------	---

I/Os and power

Non-isolated lines	2 programmable GPIOs
I/O connector	Coax, STP
Power supply	5 VDC over MIPI CSI-2
Power consumption	Value for the integrated serializer adds to CSI-2 model value.

Operating conditions

Operating temperature (housing)	-20 °C to 65 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	41 × 29 × 29
Lens mount(s)	C-Mount, CS-Mount, S-Mount
Weight	70 g


On-board memory and FPGA

Image buffer (RAM)	256 KByte
Non-volatile memory (Flash)	1024 KByte

Interfaces


Digital interface	GMSSL2, based on MIPI CSI-2, up to 4 lanes
-------------------	--

Quantum Efficiency



Technical Drawing

Alvium FP3/GM2 C-Mount Coax



Alvium FP3/GM2 C-Mount STP

