

Alvium 1800 U

Alvium 1800 U-158



Alvium 1800 U-158 innovative USB camera with Sony IMX273 CMOS global shutter sensor provides industrial performance for cost effective embedded and machine vision applications.

General

Model:	Alvium 1800 U-158
Product series:	Alvium 1800 U
Status:	Available

Sensor

Sensor type:	Area scan
Chroma:	Mono or Color
Spectrum:	Visible
Spectral range:	300 nm to 1100 nm
Resolution:	1,456 × 1,088 (1.60 MP)
Sensor model:	Sony IMX273
Sensor architecture (material):	CMOS
Shutter type(s):	Global Shutter
Sensor size:	6.30 mm diagonal (Type 1/2.9)
Pixel size:	3.45 µm × 3.45 µm

Pixel formats

Sensor bit depth:	8-bit, 10-bit, 12-bit; Adaptive (10-bit, 12-bit)
Monochrome pixel formats:	Mono8, Mono10, Mono10p, Mono12, Mono12p
YUV pixel formats:	YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr

Pixel formats

RGB pixel formats:	RGB8 (default), BGR8
Bayer pixel formats:	BayerRG8, BayerRG10, BayerRG10p, BayerRG12, BayerRG12p
Output color space:	8-bit, 10-bit, 12-bit; Adaptive (10-bit, 12-bit)

Imaging performance

Quantum efficiency @ 529 nm:	64 %
------------------------------	------

Timing and gain

Max. frame rate:	257 fps
------------------	---------

I/Os and power

Non-isolated lines:	4 programmable GPIOs
Power supply:	Power over USB 3.1 Gen 1 External power 5.0 V
Power consumption:	USB power: 2.5 W (typical) Ext. power: 2.6 W (typical)

Operating conditions

Operating temperature (housing):	-20 °C to 65 °C (housing)
----------------------------------	---------------------------

Mechanical properties

Body dimensions (L x W x H in mm):	38 × 29 × 29
Lens mount(s):	C-Mount, CS-Mount, S-Mount
Weight:	65 g

On-board memory and FPGA

Image buffer (RAM):	256 KByte
Non-volatile memory (Flash):	1024 KByte

Interfaces

Digital interface:	USB3 Vision
--------------------	-------------

Quantum Efficiency



