



Alvium 1800 U

Alvium 1800 U-1240

Alvium 1800 U-1240 innovative USB camera with Sony IMX226 rolling shutter sensor provides industrial performance for cost effective embedded and machine vision applications.

General

Model	Alvium 1800 U-1240
Product series	Alvium 1800 U
Status	Available

Sensor

Sensor type	Area scan
Chroma	Color, Mono
Spectrum	Visible
Spectral range	300 nm to 1100 nm
Resolution	4,024 × 3,036 (12.20 MP)
Sensor model	Sony IMX226
Sensor architecture (material)	cmos
Shutter type(s)	Global Reset Shutter, Rolling shutter (RS)
Sensor size	7.4 × 5.6 mm (9.3 mm, Type 1/1.7)
Pixel size	1.85 µm × 1.85 µm

Pixel formats

Sensor bit depth	10-bit
YUV pixel formats	YCbCr411_8_CbYYCrYY, YCbCr422_8_CbYCrY, YCbCr8_CbYCr
RGB pixel formats	BGR8, RGB8 (default)
Bayer pixel formats	BayerRG12

Imaging performance

Quantum efficiency @ 529 nm	74 %
-----------------------------	------

Timing and gain

Max. frame rate	35 fps
Exposure time	11 μ s to 10 s
Gain	0.0 dB to 27.0 dB

I/Os and power

Non-isolated lines	4 programmable GPIOs
Power supply	Power over USB 3.1 Gen 1 External power 5.0 V
Power consumption	USB power: 3.1 W (typical) Ext. power: 3.3 W (typical)

Operating conditions

Operating temperature (housing)	-20 °C to 65 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	38 × 29 × 29
Lens mount(s)	C-Mount, CS-Mount, S-Mount
Weight	65 g


On-board memory and FPGA

Image buffer (RAM)	256 KByte
Non-volatile memory (Flash)	1024 KByte

Interfaces

Digital interface	usb3.0
Vision standard	USB3 Vision

Quantum Efficiency



Technical Drawing

