



Alvium 1800 U

Alvium 1800 U-812 UV

Alvium 1800 U-812 UV innovative USB camera with Sony IMX487 global shutter sensor provides industrial performance for cost effective embedded and machine vision applications.

General

Model	Alvium 1800 U-812 UV
Product series	Alvium 1800 U
Status	Available

Sensor

Sensor type	Area scan
Chroma	Mono
Spectrum	UV
Spectral range	200 nm to 1100 nm
Resolution	2,848 × 2,848 (8.10 MP)
Sensor model	Sony IMX487
Sensor architecture (material)	cmos
Shutter type(s)	Global shutter (GS)
Sensor size	7.8 × 7.8 mm (11 mm, Type 2/3)
Pixel size	2.74 µm × 2.74 µm

Pixel formats

Sensor bit depth	12-bit
Monochrome pixel formats	Mono8 (default)

Timing and gain

Max. frame rate	51 fps
-----------------	--------

I/Os and power

Non-isolated lines	4 programmable GPIOs
Power supply	Power over USB 3.1 Gen 1 External power 5.0 V
Power consumption	USB power: 3.9 W (typical) Ext. power: 4.1 W (typical)

Operating conditions

Operating temperature (housing)	-20 °C to 65 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	38 × 29 × 29
Lens mount(s)	C-Mount, CS-Mount
Weight	65 g


On-board memory and FPGA

Image buffer (RAM)	256 KByte
Non-volatile memory (Flash)	1024 KByte

Interfaces

Digital interface	usb3.0
Vision standard	USB3 Vision

Quantum Efficiency



Technical Drawing

