

# Alvium 1500 C

## Alvium 1500 C-120

Alvium C-1500-120 innovative MIPI CSI-2 camera with ON Semi AR0135CS CMOS global shutter sensor provides industrial performance for cost effective embedded applications.

### General

Model:	Alvium 1500 C-120
Product series:	Alvium 1500 C
Status:	Available

### Sensor

Sensor type:	Area scan
Chroma:	Mono or Color
Spectrum:	Visible
Spectral range:	300 nm to 1100 nm
Resolution:	1,280 × 960 (1.20 MP)
Sensor model:	ON Semi AR0135CS
Shutter type(s):	Global Shutter
Sensor size:	6.09 mm ø (Type 1/3)
Pixel size:	3.75 µm × 3.75 µm

### Pixel formats

Monochrome pixel formats:	GREY, RAW10, RAW12, RAW8, Y10, Y12
YUV pixel formats:	UYVY, YUV422 8-bit
RGB pixel formats:	RGB3, RGB888 (default)

### Imaging performance

Quantum efficiency @ 529 nm:	69 %
------------------------------	------

### Timing and gain

Max. frame rate:	52 fps
Exposure time:	57 µs to 8 s
Gain:	0.0 dB to 17.7 dB

## I/Os and power

Non-isolated lines:	2 programmable GPIOs
Power supply:	5 VDC over MIPI CSI-2
Power consumption:	Typical: 1.1 W

## Operating conditions

Operating temperature (housing):	-20 °C to 65 °C (housing)
----------------------------------	---------------------------

## Mechanical properties

Body dimensions (L x W x H in mm):	26 × 29 × 29
Lens mount(s):	C-Mount, CS-Mount, S-Mount
Weight:	40 g

## On-board memory and FPGA

Image buffer (RAM):	256 KByte
Non-volatile memory (Flash):	1024 KByte

## Interfaces

Digital interface:	MIPI CSI-2, up to 4 lanes
--------------------	---------------------------

# Quantum Efficiency



