

EoSens CoaXPress-12

EoSens21MCX12-M58



General

Model:	EoSens21MCX12-M58
Product code:	F006217
Product series:	EoSens CoaXPress-12
Status:	Available

Sensor

Sensor type:	Area scan
Chroma:	Mono
Spectrum:	Visible
Spectral range:	350 nm to 1000 nm
Resolution:	5,120 × 4,096 (21.00 MP)
Sensor model:	Gpixel Gsprint 4521
Sensor architecture (material):	cmos
Shutter type(s):	global-shutter
Sensor size:	23.04 × 18.43 mm (29.51 mm, 29.5mm)
Pixel size:	4.50 μm × 4.50 μm

Pixel formats

Sensor bit depth:	8-Bit,10-Bit,12-Bit
Monochrome pixel formats:	mono8, mono10, mono12

Timing and gain

Max. frame rate:	230
Max. frame rate ROI modes:	5120 x 4096 230 fps, 5120 x 3072 305 fps, 5120 x 1024 891 fps, 5120 x 128 5540 fps, x 12560 fps,
Exposure time:	4 μ s to 1 s
Gain:	0.0 dB to 12.0 dB

I/Os and power

Non-isolated lines:	0 x LVDS input, 0 x LVDS output, 0 x TTL input, 0 x TTL output, 2 x 24V input, 0 x Open drain output,
Specific non-isolated lines:	0 x RS232 input, 0 x RS232 output, 0 x RS422 input, 0 x RS422 output,
Opto-isolated lines:	0 x Optical isolated input, 0 x Optical isolated input,
I/O connector:	2
Power supply:	12 to 24VDC
Power consumption:	External: 21 W (typical)

Operating conditions

Operating temperature (housing):	-10 °C to 60 °C
----------------------------------	-----------------

Mechanical properties

Body dimensions (L x W x H in mm):	55 x 80 x 80
IP class:	IP30
Lens mount(s):	M58x0.75
Weight:	630 g

Interfaces

Digital interface:	cxp-12 with 4 connections
Interface connector:	(micro-BNC)

FW features - image control

Exposure modes:	external
Gain modes:	Digital, Analog
White balance modes:	true
Image control features:	FW Features - Image Control