

# Alvium 1800 U

Alvium 1800 U-320 VSWIR



Alvium 1800 U-320 VSWIR innovative USB camera with Sony IMX993 SenSWIR InGaAs global shutter sensor provides industrial performance for cost effective embedded and machine vision applications.

## General

Model:	Alvium 1800 U-320 VSWIR
Product series:	Alvium 1800 U
Status:	Available

## Sensor

Sensor type:	Area scan
Chroma:	Mono
Spectrum:	SWIR, Visible SWIR
Spectral range:	400 nm to 1700 nm
Resolution:	2,080 × 1,544 (3.20 MP)
Sensor model:	Sony IMX993   InGaAs
Sensor architecture (material):	InGaAs
Shutter type(s):	Global Shutter
Sensor size:	9 mm ø (Type 1/1.8)
Pixel size:	3.45 µm × 3.45 µm

## Pixel formats

Sensor bit depth:	8-bit, 10-bit, 12-bit; Adaptive (10-bit, 12-bit)
Monochrome pixel formats:	Mono8 (default), Mono10, Mono10p, Mono12, Mono12p

## Timing and gain

Max. frame rate: 123

## I/Os and power

Non-isolated lines: 4 programmable GPIOs

Power supply: Power over USB 3.1 Gen 1 | External power 5.0 V

Power consumption: USB power: 2.8 W (typical) | External power: 2.8 W (typical)

## Operating conditions

Operating temperature (housing): -20 °C to 65 °C (housing)

## Mechanical properties

Body dimensions (L x W x H in mm): 38 × 29 × 29

Lens mount(s): C-Mount, CS-Mount

Weight: 65 g

## On-board memory and FPGA

Image buffer (RAM): 256 KByte

Non-volatile memory (Flash): 1024 KByte

## Interfaces

Digital interface: usb3.0

Vision standard: USB3 Vision

# Quantum Efficiency



