

# Alvium 1500 C

Alvium 1500 C-050

Alvium 1500 C-050 innovative MIPI CSI-2 camera with ON Semi PYTHON 480 CMOS global shutter sensor provides industrial performance for cost effective embedded applications.

## General

Model:	Alvium 1500 C-050
Product series:	Alvium 1500 C
Status:	Available

## Sensor

Sensor type:	Area scan
Chroma:	Mono or Color
Spectrum:	Visible
Spectral range:	300 nm to 1100 nm
Resolution:	800 × 600 (0.50 MP)
Sensor model:	ON Semi PYTHON 480
Shutter type(s):	Global Shutter
Sensor size:	4.9 mm ø (Type 1/3.6)
Pixel size:	4.80 µm × 4.80 µm

## Pixel formats

Monochrome pixel formats:	GREY, RAW10, RAW12, RAW8, Y10, Y12
YUV pixel formats:	UYVY, YUV422 8-bit
RGB pixel formats:	RGB3, RGB888 (default)

## Imaging performance

Quantum efficiency @ 529 nm:	53 %
------------------------------	------

## Timing and gain

Max. frame rate:	117 fps
Exposure time:	64 µs to 10 s
Gain:	0.0 dB to 11.3 dB

## I/Os and power

Non-isolated lines:	2 programmable GPIOs
Power supply:	5 VDC over MIPI CSI-2
Power consumption:	Typical: 1.3 W

## Operating conditions

Operating temperature (housing):	-20 °C to 65 °C (housing)
----------------------------------	---------------------------

## Mechanical properties

Body dimensions (L x W x H in mm):	26 × 29 × 29
Lens mount(s):	C-Mount, CS-Mount, S-Mount
Weight:	40 g

## On-board memory and FPGA

Image buffer (RAM):	256 KByte
Non-volatile memory (Flash):	1024 KByte

## Interfaces

Digital interface:	MIPI CSI-2, up to 4 lanes
--------------------	---------------------------

# Quantum Efficiency



