

EoSens CoaXPress- 12

EoSens2.0CCX12-FM



General

Model:	EoSens2.0CCX12-FM
Product code:	F006010
Product series:	EoSens CoaXPress-12
Status:	Available

Sensor

Sensor type:	Area scan
Chroma:	Color
Spectrum:	Visible
Spectral range:	400 nm to 1000 nm
Resolution:	1,920 × 1,080 (2.00 MP)
Sensor model:	Luxima Lux19HS
Sensor architecture (material):	cmos
Shutter type(s):	global-shutter
Sensor size:	19.2 × 10.8 mm (22.03 mm, 4/3)
Pixel size:	10.00 μm × 10.00 μm

Pixel formats

Sensor bit depth:	8-Bit,10-Bit
RGB pixel formats:	bayer8, bayer10

Timing and gain

Max. frame rate:	2247
Max. frame rate ROI modes:	1920 x 1080 2247 fps, 1024 x 768 3152 fps, 640 x 480 5020 fps, 128 x 128 18177 fps, 1920 x 8 170578 fps, x 170575 fps,
Exposure time:	2 μ s to 1 s
Gain:	0.0 dB to 18.0 dB

I/Os and power

Non-isolated lines:	0 x LVDS input, 0 x LVDS output, 0 x TTL input, 0 x TTL output, 2 x 24V input, 0 x Open drain output,
Specific non-isolated lines:	0 x RS232 input, 0 x RS232 output, 0 x RS422 input, 0 x RS422 output,
Opto-isolated lines:	0 x Optical isolated input, 0 x Optical isolated input,
I/O connector:	2
Power supply:	12 to 24VDC, Power over CoaXPress
Power consumption:	External: 13 W (typical)

Operating conditions

Operating temperature (housing):	-10 °C to 65 °C
----------------------------------	-----------------

Mechanical properties

Body dimensions (L x W x H in mm):	84 x 80 x 80
Filter/protection glass:	UV/IR Filter
IP class:	IP30
Lens mount(s):	F-Mount
Weight:	550 g

Interfaces

Digital interface:	cxp-12 with 4 connections
Interface connector:	(micro-BNC)

FW features - image control

Exposure modes:	external
Gain modes:	Digital, Analog
Image control features:	FW Features - Image Control

FW features - camera control

Trigger modes/sync:	External TTL Signal, CXP-Trigger
---------------------	----------------------------------

