



EXO USB3

exo4000MU3

General

Model	exo4000MU3
Product code	F001627
Product series	EXO USB3
Status	Available

Sensor

Sensor type	Area scan
Chroma	Mono
Spectrum	Visible
Spectral range	400 nm to 1000 nm
Resolution	2,048 × 2,048 (4.00 MP)
Sensor model	CMOSIS/ams CMV4000
Sensor architecture (material)	cmos
Shutter type(s)	Global shutter (GS)
Sensor size	11.26 × 11.26 mm (15.93 mm, 15.9mm (1"))
Pixel size	5.50 µm × 5.50 µm

Pixel formats

Sensor bit depth	8-bit, 12-bit
Monochrome pixel formats	mono8, mono12packed

Imaging performance

Dynamic range	52 dB
SNR	38 dB

Timing and gain

Max. frame rate	74 fps
Exposure time	27 μ s to 10 s
Gain	0.0 dB to 11.0 dB

I/Os and power

Non-isolated lines	0 x LVDS input, 0 x LVDS output, 0 x TTL input, 0 x TTL output, 2 x 24V input, 4 x Open drain output,
Specific non-isolated lines	1 x RS232 input, 1 x RS232 output, 0 x RS422 input, 0 x RS422 output,
Opto-isolated lines	1 x Optical isolated input, 0 x Optical isolated input,
Power supply	10 to 25VDC
Power consumption	External: 4.5 W (typical)

Mechanical properties

Body dimensions (L x W x H in mm)	47 x 50 x 50
Filter/protection glass	K9 - AR coating - 400-850nm
IP class	IP40
Lens mount(s)	C-Mount
Weight	138 g

On-board memory and FPGA

Image buffer (RAM)	192 MByte
Non-volatile memory (Flash)	32 MByte

Interfaces

Digital interface	usb3.0
Interface connector	(Micro-B)

FW features - image control

Exposure modes	manual, auto, external
Gain modes	auto, manual
Image control features	roi, lut, mirror-image, dpc, shading-correction


FW features - camera control

Trigger modes/sync	internal, software, external
--------------------	------------------------------


FW features - camera control

Camera control features	User Sets, PWM(4), Sequencer,
-------------------------	-------------------------------


Quantum Efficiency




[back](#)





right side



top




bottom



I/O pin assignment

Hirose 12 Pin



1	VIN -	(GND)	7	OUT 1	(open drain)
2	VIN +	(10 V to 25 V DC)	8	OUT 2	(open drain)
3	IN 4	(RXD RS232)	9	IN 3 +	(opto In +)
4	OUT 4	(TXD RS232)	10	IN 3 -	(opto In -)
5	IN 1	(0-24V)	11	OUT 3	(open drain)
6	IN 2	(0-24V)	12	OUT 0	(open drain)