

FXO 25GigE

fxo425C25GE



General

Model	fxo425C25GE
Product code	F002297
Product series	FXO 25GigE
Status	Available

Sensor

Sensor type	Area scan
Chroma	Color
Spectrum	Visible
Spectral range	400 nm to 1000 nm
Resolution	1,600 × 1,104 (1.80 MP)
Sensor model	Sony IMX425
Sensor architecture (material)	cmos
Shutter type(s)	global-shutter
Sensor size	14.4 × 9.94 mm (17.5 mm, 17.6mm (Type 1.1))
Pixel size	9.00 μm × 9.00 μm

Pixel formats

RGB pixel formats	bayer12, bayer8
-------------------	-----------------

Timing and gain

Max. frame rate	671 fps
Exposure time	6 μs to 60 s
Gain	0.0 dB to 48.0 dB

I/Os and power

Non-isolated lines	0 x LVDS input, 0 x LVDS output, 0 x TTL input, 0 x TTL output, 2 x 24V input, 4 x Open drain output,
Specific non-isolated lines	1 x RS232 input, 1 x RS232 output, 0 x RS422 input, 0 x RS422 output,
Opto-isolated lines	1 x Optical isolated input, 0 x Optical isolated input,
Power supply	10 to 25VDC
Power consumption	External: 17 W (typical)

Operating conditions

Operating temperature (housing)	-10 °C to 60 °C
---------------------------------	-----------------

Mechanical properties

Body dimensions (L x W x H in mm)	100 × 50 × 50
Filter/protection glass	IR-Cut 680
IP class	IP30
Lens mount(s)	C-Mount
Weight	320 g

On-board memory and FPGA

Image buffer (RAM)	4032 MByte
Non-volatile memory (Flash)	128 MByte


Interfaces

Digital interface	25gige
Interface connector	(SFP28)


FW features - image control

White balance modes	auto, manual
---------------------	--------------

Quantum Efficiency



I/O pin assignment

 <p>Hirose 12 Pin</p>	1	VIN - (GND)	7	OUT 1 (open drain)
	2	VIN + (10 V to 25 V DC)	8	OUT 2 (open drain)
	3	IN 4 (RXD RS232)	9	IN 3 + (opto In +)
	4	OUT 4 (TXD RS232)	10	IN 3 - (opto In -)
	5	IN 1 (0-24V)	11	OUT 3 (open drain)
	6	IN 2 (0-24V)	12	OUT 0 (open drain)