



Goldeye Pro

Goldeye Pro G5-320 VSWIR TEC1

Goldeye Pro G5-320 VSWIR TEC1 5GBASE-T camera with global shutter Sony IMX993 SenSWIR InGaAs sensor enables short wave infrared (SWIR) imaging with industrial performance for various machine vision applications.

General

Model:	Goldeye Pro G5-320 VSWIR TEC1
Product series:	Goldeye Pro
Status:	Available

Sensor

Sensor type:	Area scan
Spectrum:	SWIR, Visible SWIR
Spectral range:	400 nm to 1700 nm
Resolution:	2,080 × 1,544 (3.20 MP)
Sensor model:	Sony IMX993 InGaAs
Sensor architecture (material):	InGaAs
Shutter type(s):	Global Shutter
Sensor size:	9 mm ø (Type 1/1.8)
Pixel size:	3.45 µm × 3.45 µm

Pixel formats

Monochrome pixel formats:	Mono12 (default)
---------------------------	------------------

Timing and gain

Max. frame rate:	159 fps
------------------	---------

I/Os and power

Non-isolated lines:	4 bidirectional I/O lines
Opto-isolated lines:	1 input, 3 outputs
Power supply:	12 VDC to 24 VDC (±10%) or via PoE

I/Os and power

Power consumption: Max: 11 W (12 to 24 VDC); 12.9 W (PoE)

Operating conditions

Operating temperature (housing): 55 °C (max) (housing)

Mechanical properties

Body dimensions (L x W x H in mm): 78 × 55 × 55

Weight: 350 g

On-board memory and FPGA


Image buffer (RAM): 256 MByte

Non-volatile memory (Flash): 4 KByte

Interfaces

Digital interface: IEEE 802.3: 5GBASE-T or 2.5GBASE-T (NBASE-T) and 1000BASE-T,
IEEE 802.3af Power Class 0 PoE

Quantum Efficiency



Technical Drawing

