

Goldeye CL

Goldeye CL-032 SWIR TEC1

The Goldeye CL-032 TEC1 is a very versatile SWIR camera for the spectral range from 900 nm to 1700 nm. High frame rates of 100 fps at full resolution (636 × 508), a strong sensor cooling, as well as a high intra-scene dynamic range of more than 73 dB enable to apply the camera in various application areas and

General

Model	Goldeye CL-032 SWIR TEC1
Product series	Goldeye CL
Status	Available

Sensor

Sensor type	Area scan
Chroma	Mono
Spectrum	SWIR
Spectral range	900 nm to 1700 nm
Resolution	636 × 508 (0.30 MP)
Sensor model	FPA 636 × 508 25 µm InGaAs
Sensor architecture (material)	cmos-ingaas
Sensor size	15.9 × 12.7 mm (20.35 mm, 20.35 mm (diagonal))
Pixel size	25.00 µm × 25.00 µm

Pixel formats

Sensor bit depth	14-bit
------------------	--------

Timing and gain

Max. frame rate	100 fps
Exposure time	6 µs to 200.00 ms
Gain	0.0 dB to 34.0 dB

I/Os and power

Non-isolated lines	LVTTTL I/Os: 1 input, 1 output
Specific non-isolated lines	115 200 Baud, 8N1 (adjustable)

I/Os and power

Opto-isolated lines	1 input, 2 outputs
Power supply	10.8 V to 30.0 V
Power consumption	10 W at 12 VDC

Operating conditions

Operating temperature (housing)	-20 °C to 55 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	78 × 55 × 55
Weight	340 g


On-board memory and FPGA

Image buffer (RAM)	256 MByte
--------------------	-----------

Interfaces

Digital interface	Camera Link Base
-------------------	------------------

Quantum Efficiency



Technical Drawing

 Technical Drawing