

Goldeye CL

Goldeye CL-130 VSWIR TEC1

The Goldeye CL-130 TEC1 is an SXGA resolution short wave infrared (SWIR) camera with Camera Link interface. Frame rates up to 100 fps at full resolution enable you to access versatile application fields and to speed up your processes.

General

Model	Goldeye CL-130 VSWIR TEC1
Product series	Goldeye CL
Status	Available

Sensor

Sensor type	Area scan
Chroma	Mono
Spectrum	SWIR, Visible SWIR
Spectral range	400 nm to 1700 nm
Resolution	1,280 × 1,024 (1.30 MP)
Sensor model	Sony IMX990 InGaAs TEC
Sensor architecture (material)	cmos-ingaas
Shutter type(s)	Global shutter (GS)
Sensor size	6.4 × 5.12 mm (8.2 mm, Type 1/2)
Pixel size	5.00 µm × 5.00 µm

Pixel formats

Sensor bit depth	12-bit
------------------	--------

Timing and gain

Max. frame rate	94 fps
Exposure time	3 µs to 200.00 ms
Gain	0.0 dB to 18.0 dB

I/Os and power

Non-isolated lines	1 input, 1 output
Specific non-isolated lines	115 200 Baud, 8N1 (adjustable)

I/Os and power

Opto-isolated lines	1 input, 2 outputs
Power supply	10.8 V to 30.0 V
Power consumption	Maximum: 11.8 W (at 12 VDC)

Operating conditions

Operating temperature (housing)	-20 °C to 55 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	78 × 55 × 55
Weight	330 g


On-board memory and FPGA

Image buffer (RAM)	256 MByte
--------------------	-----------

Interfaces

Digital interface	Camera Link Base
-------------------	------------------

Quantum Efficiency



Technical Drawing

