



Goldeye G

Goldeye G-032 SWIR TEC1

The Goldeye G-032 TEC1 is a very versatile shortwave infrared camera for the spectral range from 900 nm to 1700 nm. High frame rates of 100 fps at full resolution (636 x 508), strong sensor cooling, as well as a high intra-scene dynamic range of more than 73 dB enable to apply the camera in various application areas

General

Model:	Goldeye G-032 SWIR TEC1
Product series:	Goldeye G
Status:	Available

Sensor

Sensor type:	Area scan
Chroma:	Mono
Spectrum:	SWIR
Spectral range:	900 nm to 1700 nm
Resolution:	636 × 508 (0.30 MP)
Sensor model:	FPA 636 × 508 25 µm InGaAs
Sensor architecture (material):	InGaAs
Sensor size:	20.3 mm ø (20.3 mm (diagonal))
Pixel size:	25.00 µm × 25.00 µm

Pixel formats

Sensor bit depth:	8-bit to 14-bit
Monochrome pixel formats:	Mono8, Mono12, Mono12Packed, Mono14

Timing and gain

Max. frame rate:	100 fps
------------------	---------

I/Os and power

Non-isolated lines:	LVTTTL I/Os: 1 Input, 1 Output
---------------------	--------------------------------

I/Os and power

Specific non-isolated lines:	115 200 Baud, 8N1 (adjustable)
Opto-isolated lines:	1 Input, 2 Outputs
Power supply:	10.8 V to 30.0 V or via PoE
Power consumption:	10.8 W at 12 VDC; <12.95 W PoE

Operating conditions

Operating temperature (housing):	-20 °C to 55 °C (housing)
----------------------------------	---------------------------

Mechanical properties

Body dimensions (L x W x H in mm):	78 × 55 × 55
Weight:	370 g

On-board memory and FPGA

Image buffer (RAM):	256 MByte
Non-volatile memory (Flash):	262 MByte

Interfaces

Digital interface:	IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)
--------------------	---

Goldeye G/CL-032 Absolute QE



