

Goldeye G

Goldeye G-034 XSWIR 2.2 TEC2

Goldeye G-034 XSWIR 2.2 TEC2 high-speed camera is the fastest VGA resolution extended short wave infrared camera (XSWIR) with GigE Vision interface. Frame rates up to 303 fps at full resolution enable you to access versatile application fields and to speed up your processes.

General

Model	Goldeye G-034 XSWIR 2.2 TEC2
Product series	Goldeye G
Status	Available

Sensor

Sensor type	Area scan
Chroma	Mono
Spectrum	eXtended SWIR, SWIR
Spectral range	1200 nm to 2200 nm
Resolution	636 × 508 (0.30 MP)
Sensor model	FPA 636 × 508 15 µm Extended Range InGaAs
Sensor architecture (material)	cmos-ingaas
Sensor size	9.54 × 7.62 mm (12.21 mm, 12.21 mm (diagonal))
Pixel size	15.00 µm × 15.00 µm

Pixel formats

Sensor bit depth	14-bit
------------------	--------

Timing and gain

Max. frame rate	303 fps
Exposure time	1 µs to 10.00 ms
Gain	0.0 dB to 33.0 dB

I/Os and power

Non-isolated lines	LVTTL I/Os: 1 input, 1 output
--------------------	-------------------------------

I/Os and power

Specific non-isolated lines	115 200 Baud, 8N1 (adjustable)
Opto-isolated lines	1 Input, 2 Outputs
Power supply	10.8 V DC to 30.0 V or via PoE
Power consumption	21 W (at 12 VDC), <23 W (PoE)

Operating conditions

Operating temperature (housing)	-20 °C to 55 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	90 × 80 × 80
Weight	740 g


On-board memory and FPGA

Image buffer (RAM)	256 MByte
Non-volatile memory (Flash)	262 MByte

Interfaces

Digital interface	IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)
-------------------	---

Quantum Efficiency



Technical Drawing

