

Goldeye CL

Goldeye CL-033 SWIR TEC1

The Goldeye CL-033 TEC1 high-speed camera is one of the fastest VGA resolution short wave infrared (SWIR) cameras with Camera Link interface. Frame rates up to 301 fps at full resolution enable you to access versatile application fields and to speed up your processes.

General

Model	Goldeye CL-033 SWIR TEC1
Product series	Goldeye CL
Status	Available

Sensor

Sensor type	Area scan
Chroma	Mono
Spectrum	SWIR
Spectral range	900 nm to 1700 nm
Resolution	640 × 512 (0.30 MP)
Sensor model	FPA 640 × 512 15 µm InGaAs
Sensor architecture (material)	InGaAs
Sensor size	12.3 mm ø (12.3mm (diagonal))
Pixel size	15.00 µm × 15.00 µm

Pixel formats

Sensor bit depth	8-bit to 14-bit
Monochrome pixel formats	Tap Geometry 1X 1Y: Mono8, Mono12, Mono14; Tap Geometry 1X2 1Y: Mono8

Timing and gain

Max. frame rate	301 fps
-----------------	---------

I/Os and power

Non-isolated lines	LVTTL I/Os: 1 input, 1 output
Specific non-isolated lines	115 200 Baud, 8N1 (adjustable)

I/Os and power

Opto-isolated lines	1 input, 2 outputs
Power supply	10.8 V to 30.0 V
Power consumption	11.8 W at 12 VDC

Operating conditions

Operating temperature (housing)	-20 °C to 55 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	78 × 55 × 55
Weight	350 g

On-board memory and FPGA


Image buffer (RAM)	256 MByte
--------------------	-----------

Interfaces

Digital interface	Camera Link Base
-------------------	------------------

Quantum Efficiency

Goldeye G/CL-033 Absolute QE



Technical Drawing

