

Goldeye CL

Goldeye CL-034 XSWIR 1.9 TEC2

Goldeye CL-034 XSWIR 1.9 TEC2 high-speed camera is the fastest VGA resolution extended short wave infrared camera (XSWIR) with GigE Vision interface. Frame rates up to 303 fps at full resolution enable you to access versatile application fields and to speed up your processes.

General

Model	Goldeye CL-034 XSWIR 1.9 TEC2
Product series	Goldeye CL
Status	Available

Sensor

Sensor type	Area scan
Chroma	Mono
Spectrum	SWIR, eXtended SWIR
Spectral range	1100 nm to 1900 nm
Resolution	636 × 508 (0.32 MP)
Sensor model	Progressive scan 0.32 MP
Sensor architecture (material)	cmos-ingaas
Shutter type(s)	Global shutter (GS)
Sensor size	9.54 × 7.62 mm (12.2 mm, Type 1)
Pixel size	15.00 µm × 15.00 µm

Pixel formats

Sensor bit depth	14-bit
Monochrome pixel formats	Tap geometry 1X 1Y: Mono8, Tap geometry 1X2 1Y: Mono8

Timing and gain

Max. frame rate	303 fps
Exposure time	1 µs to 20.00 ms
Gain	0.0 dB to 33.0 dB

I/Os and power

Non-isolated lines	LVTTTL I/Os: 1 input, 1 output
Specific non-isolated lines	115 200 Baud, 8N1 (adjustable)
Opto-isolated lines	1 input, 2 outputs
Power supply	10.8 V to 30.0 V
Power consumption	21 W at 12 VDC

Operating conditions

Operating temperature (housing)	-20 °C to 55 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm)	90 × 80 × 80
Weight	740 g


On-board memory and FPGA

Image buffer (RAM)	256 MByte
--------------------	-----------

Interfaces

Digital interface	Camera Link Base
-------------------	------------------

Quantum Efficiency



Technical Drawing

