

Goldeye G

Goldeye G-008 SWIR TEC1



The Goldeye G-008 TEC1 is a short wave infrared (SWIR) camera running 344 fps at 1/4-VGA resolution. Its GigE Vision interface enables fast integration for versatile applications at an affordable price.

General

Model:	Goldeye G-008 SWIR TEC1
Product series:	Goldeye G
Status:	Available

Sensor

Sensor type:	Area scan
Chroma:	Mono
Spectrum:	SWIR
Spectral range:	900 nm to 1700 nm
Resolution:	320 × 256 (0.10 MP)
Sensor model:	FPA 320 × 256 30 µm InGaAs
Sensor architecture (material):	InGaAs
Sensor size:	12.3 mm ø (12.3mm (diagonal))
Pixel size:	30.00 µm × 30.00 µm

Pixel formats

Sensor bit depth:	8-bit to 14-bit
Monochrome pixel formats:	Mono8, Mono10, Mono10p, Mono10Packed, Mono12, Mono12p, Mono12Packed, Mono14, Mono16

Timing and gain

Max. frame rate: 344

I/Os and power

Non-isolated lines: LVTTTL I/Os: 1 Input, 1 Output

Specific non-isolated lines: 115 000 Baud, 8N1 (adjustable)

Opto-isolated lines: 1 Input, 2 Outputs

Power supply: 10.8 V to 30.0 V or via PoE

Power consumption: 10.8 W (at 12 VDC), <12.95 W (PoE)

Operating conditions

Operating temperature (housing): -20 °C to 55 °C (housing)

Mechanical properties

Body dimensions (L x W x H in mm): 78 × 55 × 55

Weight: 340 g

On-board memory and FPGA

Image buffer (RAM): 256 MByte

Non-volatile memory (Flash): 262 MByte

Interfaces

Digital interface: IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)

Goldeye G/CL-008 Absolute QE



