

Goldeye G

Goldeye G-130 VSWIR TEC1

Goldeye G-130 TEC1 is a fast SXGA resolution short wave infrared (SWIR) camera with GigE Vision interface. Frame rates up to 94 fps at full resolution enable you to access versatile application fields and to speed up your processes.

General

Model	Goldeye G-130 VSWIR TEC1
Product series	Goldeye G
Status	Available

Sensor

Sensor type	Area scan
Spectrum	SWIR, Visible SWIR
Spectral range	400 nm to 1700 nm
Resolution	1,280 × 1,024 (1.30 MP)
Sensor model	Sony IMX990 InGaAs TEC
Sensor architecture (material)	InGaAs
Shutter type(s)	Global Shutter
Sensor size	8.15 mm ø (Type 1/2)
Pixel size	5.00 µm × 5.00 µm

Timing and gain

Max. frame rate	94 fps
-----------------	--------

I/Os and power

Non-isolated lines	1 input, 1 output
Specific non-isolated lines	115 200 Baud, 8N1 (adjustable)
Opto-isolated lines	1 input, 2 outputs
Power supply	10.8 V DC to 30.0 V or via PoE
Power consumption	Maximum: 10.8 W (at 12 VDC), <12.95 W (PoE)

Operating conditions

Operating temperature (housing)	-20 °C to 55 °C ((housing))
---------------------------------	-----------------------------

Mechanical properties

Body dimensions (L x W x H in mm) 78 × 55 × 55

Weight 340 g

On-board memory and FPGA


Image buffer (RAM) 256 MByte

Non-volatile memory (Flash) 262 MByte

Interfaces

Digital interface IEEE 802.3 1000BASE-T, IEEE 802.3af (PoE)

Quantum Efficiency



Technical Drawing

